

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

SE series

|                                    |                                                                         |
|------------------------------------|-------------------------------------------------------------------------|
| Number of contacts Low Voltage     | 10                                                                      |
| Wire Size/AWG                      | 30 - 22                                                                 |
| Socket / Receptacle                | Socket / Receptacle - Free                                              |
| Locking system                     | Push-pull                                                               |
| Jacket cable outside diameter [mm] | 4.30 - 5.20 mm                                                          |
| Size                               | 2S                                                                      |
| Suggested matching part            | <a href="#">FGZ.2S.310.CLAD52</a><br><a href="#">FGZ.2S.310.CLAD52Z</a> |
| Series                             | S - Indoor Stepped Insert                                               |

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/pgz-2s-310-clld52.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pgz-2s-310-clld52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Number of contacts Low Voltage          | 10                            |
| Contact Termination Low voltage         | Solder                        |
| R (max) - electrical contact resistance | 4.8 mOhm                      |
| Insert configuration value              | 2S.310 - 10 Low Voltage       |
| Insulator                               | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                           | 7 A                           |
| Test voltage (kV DC)                    | 1.2                           |
| Max. Solid Conductor                    | 0.34 mm <sup>2</sup> (AWG 22) |
| Bucket Dia.                             | 0.8 mm (0.031 in)             |
| Contact Dia.                            | 0.9 mm (0.035 in)             |
| Wire Size/AWG                           | 30 - 22                       |

## Form & Material

|                        |                                                                                                                               |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell style / Model id | PGZ - Free socket, - design chocolate block, cable collet                                                                     |
| Socket / Receptacle    | Free                                                                                                                          |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system         | Push-pull                                                                                                                     |
| Keying                 | Hermaphroditic keying (half moon insert) with female pin 1                                                                    |
| Colour                 | Grey                                                                                                                          |
| Weight                 | 27.81 g                                                                                                                       |

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/pgz-2s-310-clld52.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pgz-2s-310-clld52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

|                                   |                                                                         |
|-----------------------------------|-------------------------------------------------------------------------|
| Technical domain                  | Audio Video, Energy and Industrial, Semiconductor, Test and Measurement |
| Environmental sealing (IP rating) | IP50                                                                    |
| Endurance                         | 5000 mating cycles                                                      |
| Temperature range                 | -55°C / +250°C (max. temperature valid for short periods of use.)       |
| Climatic Category                 | 55/175/21                                                               |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]                                              |
| Shielding (min)                   | 75 dB (10 MHz)                                                          |
| Shielding (min)                   | 40 dB (1 GHz)                                                           |
| Shock Resistance                  | 100 g [ 6 ms]                                                           |
| Vibration                         | 15 g [10 Hz - 2000 Hz]                                                  |
| Salt Spray Corrosion              | >1000 hr                                                                |

Cable fixation

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Cable termination protection       | Standard back nut (no additional protection) |
| Jacket cable outside diameter [mm] | 4.30 - 5.20 mm                               |

Drawings



Dimensions

|     | A    | L    | S1   | S2   |
|-----|------|------|------|------|
| mm. | 16.5 | 47   | 13   | 12   |
| in. | 0.65 | 1.85 | 0.51 | 0.47 |

# Recommended By Lemo

## Caps

Soft Cap

BPZ.2B.200.SCN

# Cables

| Cable PartNumber   | Material | Colour | Cable image                                                                         |
|--------------------|----------|--------|-------------------------------------------------------------------------------------|
| CMN.10.T28.052PGZE |          | grey   |  |
| CMN.10.T28.052PNZE |          |        |  |
| 110260             | PTFE     | White  |  |