

Standard

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[BKT series](#)

Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	7.10 - 7.50 mm
Size	2T
Suggested matching part	<a href="#">FGG.2T.316.CLAC75</a>
Series	T - Small Outdoor keyed

# Technical details

## Electrical Configuration

R (max)	6.1 mOhm
Footprint IPC Class3 compatibility	No
Rated current	6 A
Vtest (contact-contact)	1.4 kV (DC)
Vtest (contact-shell)	1.8 kV (DC)
Max. Solid Conductor	0.34 mm <sup>2</sup> (AWG 22)
Max. Stranded Conductor	0.34 mm <sup>2</sup> (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	30 - 22
Gender	Standard

## Form & Material

Shell style / Model id	PH - Free receptacle, cable collet and nut for fitting a bend relief
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	33.1 g

## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Resistance to vibration	15 g [10 Hz - 2000 Hz]
Shock Resistance	100 g [ 6 ms]
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/originals/t-outdoor-keyed/phg-2t-316-cllc75z.html](https://www.lemo.com/int_en/solutions/originals/t-outdoor-keyed/phg-2t-316-cllc75z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	7.10 - 7.50 mm

## Drawings



## Dimensions

	A	L	S1	S2
mm.	15	51	13	12
in.	0.59	2.01	0.51	0.47

## Recommended By Lemo

### Accessories

Compatible cap	BRF.2T.200.CAZ
----------------	----------------

### Tools

Spanner	DCP.2T.110.TN
---------	---------------