



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

| | |
|------------------------------------|--|
| Number of contacts Low Voltage | 4 |
| Wire Size/AWG | 30 - 22 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Rear Mounted |
| Locking system | Push-pull |
| Jacket cable outside diameter [mm] | 1.00 - 12.60 mm |
| Size | 1P |
| Suggested matching part | PAG.M0.4TL.AC39N |
| Series | REDEL P - Push-Pull |

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage | 4 |
| Contact Termination Low voltage | Solder |
| R (max) | 4.5 mOhm |
| Insert configuration value | 1P.M04 - 4 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 8 A |
| Test voltage contact-contact | 1.7 (kV DC) |
| Max. Solid Conductor | 0.34 mm ² (AWG 22) |
| Max. Stranded Conductor | 0.34 mm ² (AWG 22) |
| Air clearance | 1.2 mm |
| Creepage distance | 1.2 mm |
| Bucket Dia. | 0.8 mm (0.031in) |
| Contact Dia. | 0.9 mm (0.0354in) |
| Wire Size/AWG | 30 - 22 |
| Gender | Standard |

Form & Material

| | |
|------------------------|--|
| Shell style / Model id | PK - Fixed receptacle with two nuts (back panel mounting) |
| Socket / Receptacle | Fixed Panel Rear Mounted |
| Housing material | PEI (Polyetherimide), black |
| Locking system | Push-pull |
| Keying | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Colour | Black |
| Variant | Black front nut |
| Weight | 4.77 g |

Environment

| | |
|-----------------------------------|--|
| Technical domain | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | > 5000 mating cycles |
| Temperature range | -50°C / +170°C |
| F ret (max) | 150 N |
| F ret (min) | 50 N |
| Steam sterilization | Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us. |

Cable fixation

| | |
|------------------------------------|-----------------|
| Jacket cable outside diameter [mm] | 1.00 - 12.60 mm |
|------------------------------------|-----------------|

Recommended By Lemo

Accessories

| | |
|----------------|-------------|
| Compatible cap | PBG.200.BMV |
|----------------|-------------|

Tools

| | |
|---------|------------|
| Spanner | POB.186.GN |
|---------|------------|

https://www.lemo.com/int_en/solutions/redeI/redeI-p-push-pull/pkg-m0-4tl-In.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|---------------|--------|--|
| CMN.04.T22.047QGC | TPR | Grey | |
| CMN.04.T22.048QGZE | TPR (medical) | Grey |  |
| CMN.04.T28.031PGCE | PVC | GREY |  |
| CMN.04.T28.031PGZE | | grey |  |
| CMN.04.T28.031PNCE | PVC | Black |  |
| CMN.04.T28.031PNZE | | |  |
| CMN.04.T28.031QGC | TPR | Grey | |
| 140240 | PVC | Black |  |
| 140250 | PVC | Grey |  |
| 40080 | PVC | Black | |
| 40086 | PVC | Blue | |
| 40140 | PVC | Black |  |
| 40240 | PTFE | White |  |
| 40260 | PVC | Black |  |
| 4041 | PVC | Grey |  |
| 4050 | PVC | Black |  |
| 4080 | PVC | Grey | |
| 417920 | PVC | Grey |  |
| 4220 | PVC | Black |  |
| 4221 | PVC | Black |  |
| 4260 | PTFE | White |  |
| 4280 | PVC | Black |  |
| 80080 | PVC | Grey | |
| 80082 | PVC | Red | |
| 80084 | PVC | Black | |
| CTR.75.030.121870G | PVC | Grey |  |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkg-m0-4tl-ln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.