



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[P series catalog](#)

|                                    |                                                                        |
|------------------------------------|------------------------------------------------------------------------|
| Number of contacts Low Voltage     | 6                                                                      |
| Wire Size/AWG                      | 32 - 24                                                                |
| Gender                             | Standard                                                               |
| Socket / Receptacle                | Socket / Receptacle - Fixed Panel Front Mounted                        |
| Locking system                     | Push-pull                                                              |
| Jacket cable outside diameter [mm] | 1.00 - 12.60 mm                                                        |
| Size                               | 1P                                                                     |
| Suggested matching part            | <a href="#">PFA.M0.6GL.AC52GZ</a><br><a href="#">PFA.M0.6GL.AC39GZ</a> |
| Series                             | REDEL P - Push-Pull                                                    |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pna-m0-6gl-lg.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pna-m0-6gl-lg.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                    |                               |
|------------------------------------|-------------------------------|
| Number of contacts Low Voltage     | 6                             |
| Contact Termination Low voltage    | Solder                        |
| R (max)                            | 6.5 mOhm                      |
| Insert configuration value         | 1P.M06 - 6 Low Voltage        |
| Footprint IPC Class3 compatibility | No                            |
| Insulator                          | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                      | 6 A                           |
| Test voltage contact-contact       | 1.48 (kV DC)                  |
| Max. Solid Conductor               | 0.25 mm <sup>2</sup> (AWG 24) |
| Max. Stranded Conductor            | 0.14 mm <sup>2</sup> (AWG 26) |
| Air clearance                      | 0.85 mm                       |
| Creepage distance                  | 0.85 mm                       |
| Bucket Dia.                        | 0.6 mm (0.024in)              |
| Contact Dia.                       | 0.7 mm (0.0275in)             |
| Wire Size/AWG                      | 32 - 24                       |
| Gender                             | Standard                      |

## Form & Material

|                        |                                                                        |
|------------------------|------------------------------------------------------------------------|
| Shell style / Model id | PN - Fixed receptacle, nut fixing, watertight                          |
| Socket / Receptacle    | Fixed Panel Front Mounted                                              |
| Housing material       | PSU (Polysulfone), grey                                                |
| Locking system         | Push-pull                                                              |
| Keying                 | A: 2 keys (alpha=40, Plug: male contacts, Receptacle: female contacts) |
| Colour                 | Grey                                                                   |
| Variant                | Grey front nut                                                         |
| Weight                 | 5.24 g                                                                 |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pna-m0-6gl-ig.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pna-m0-6gl-ig.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

|                                   |                                                                                                                                                                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV                                                                                                                                        |
| Environmental sealing (IP rating) | IP64                                                                                                                                                                                                                           |
| Endurance                         | > 5000 mating cycles                                                                                                                                                                                                           |
| Temperature range                 | -50°C / +150°C                                                                                                                                                                                                                 |
| F ret (max)                       | 150 N                                                                                                                                                                                                                          |
| F ret (min)                       | 50 N                                                                                                                                                                                                                           |
| Steam sterilization               | Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us. |

Cable fixation

|                                    |                 |
|------------------------------------|-----------------|
| Jacket cable outside diameter [mm] | 1.00 - 12.60 mm |
|------------------------------------|-----------------|

Drawings



Dimensions

|     | N    | a       |
|-----|------|---------|
| mm. | 23.3 | 2.5-4.5 |
| in. | 0.92 |         |

# Recommended By Lemo

## Accessories

Compatible cap

[PBG.200.BMV](#)

## Cables

| Cable PartNumber   | Material      | Colour | Cable image                                                                           |
|--------------------|---------------|--------|---------------------------------------------------------------------------------------|
| CMN.06.T26.037QGZE | TPR (medical) | Grey   |    |
| CMN.06.T28.031PGCE | PVC           | GREY   |    |
| CMN.06.T28.031PGZE |               | grey   |    |
| CMN.06.T28.031PNCE | PVC           | Black  |    |
| CMN.06.T28.031PNZE |               |        |    |
| CMN.06.T28.042QBCE | TPR (medical) |        |                                                                                       |
| CMN.06.T28.044PGZE |               | grey   |  |
| CMN.06.T28.044PNZE |               |        |  |
| 106240             | PTFE          | White  |  |
| 12080              | PVC           | Grey   |                                                                                       |
| 160140             | PVC           | Grey   |  |
| 160260             | PVC           | Black  |  |
| 260250             | PVC           | Grey   |  |
| 60260              | PTFE          | White  |  |
| 6280               | PVC           | Black  |  |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pna-m0-6gl-lg.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pna-m0-6gl-lg.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.