

**Special***Image for illustrative purpose only*

## Summary

[Request a quote](#)[P series catalog](#)[Industry Brochure Medical](#)

|                                    |                                                 |
|------------------------------------|-------------------------------------------------|
| Number of contacts Low Voltage     | 8                                               |
| Wire Size/AWG                      | 32 - 24                                         |
| Gender                             | Standard                                        |
| Socket / Receptacle                | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system                     | Push-pull                                       |
| Jacket cable outside diameter [mm] | 1.00 - 12.60 mm                                 |
| Size                               | 1P                                              |
| Suggested matching part            | <a href="#">PFG.M0.8NL.AC52NZ</a>               |
| Series                             | REDEL P - Push-Pull                             |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/png-m0-8nl-ln.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/png-m0-8nl-ln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Number of contacts Low Voltage          | 8                             |
| Contact Termination Low voltage         | Solder                        |
| R (max) - electrical contact resistance | 6.5 mOhm                      |
| Insert configuration value              | 1P.M08 - 8 Low Voltage        |
| Insulator                               | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                           | 5 A                           |
| Test voltage contact-contact            | 1.48 (kV DC)                  |
| Max. Solid Conductor                    | 0.25 mm <sup>2</sup> (AWG 24) |
| Max. Stranded Conductor                 | 0.14 mm <sup>2</sup> (AWG 26) |
| Air clearance                           | 0.6 mm                        |
| Creepage distance                       | 0.6 mm                        |
| Bucket Dia.                             | 0.6 mm (0.024 in)             |
| Contact Dia.                            | 0.7 mm (0.028 in)             |
| Wire Size/AWG                           | 32 - 24                       |
| Gender                                  | Standard                      |

## Form & Material

|                        |                                                                      |
|------------------------|----------------------------------------------------------------------|
| Shell style / Model id | PN - Fixed receptacle, nut fixing, watertight                        |
| Socket / Receptacle    | Fixed Panel Front Mounted                                            |
| Housing material       | PSU (Polysulfone), black                                             |
| Locking system         | Push-pull                                                            |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Colour                 | Black                                                                |
| Variant                | Black front nut                                                      |
| Weight                 | 5.45 g                                                               |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/png-m0-8nl-ln.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/png-m0-8nl-ln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

|                                   |                                                                                                                                                                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV                                                                                                                                        |
| Environmental sealing (IP rating) | IP64                                                                                                                                                                                                                           |
| Endurance                         | > 5000 mating cycles                                                                                                                                                                                                           |
| Temperature range                 | -50°C / +150°C                                                                                                                                                                                                                 |
| F ret (max)                       | 150 N                                                                                                                                                                                                                          |
| F ret (min)                       | 50 N                                                                                                                                                                                                                           |
| Steam sterilization               | Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us. |

Cable fixation

|                                    |                 |
|------------------------------------|-----------------|
| Jacket cable outside diameter [mm] | 1.00 - 12.60 mm |
|------------------------------------|-----------------|

Drawings



Dimensions

|     | N    | a       |
|-----|------|---------|
| mm. | 23.3 | 2.5-4.5 |
| in. | 0.92 |         |

# Recommended By Lemo

## Caps

|                |                             |
|----------------|-----------------------------|
| Compatible cap | <a href="#">PBG.200.BMV</a> |
| Cap 2          | <a href="#">PBG.201.BMV</a> |

## Tools

|         |                                |
|---------|--------------------------------|
| Spanner | <a href="#">DCA.91.231.7TN</a> |
|---------|--------------------------------|

# Cables

| Cable PartNumber   | Material      | Colour | Cable image                                                                           |
|--------------------|---------------|--------|---------------------------------------------------------------------------------------|
| CMN.08.T26.042QGZE | TPR (medical) | Grey   |    |
| 108240             | PTFE          | White  |    |
| 108260             | PTFE          | White  |    |
| 16080              | PVC           | Grey   |                                                                                       |
| 180260             | PVC           | Black  |  |
| 280250             | PVC           | Grey   |  |
| 335990             | PVC           | Black  |  |
| 335991             | PVC           | Black  |  |
| 42265              | PVC           | Yellow |                                                                                       |
| 80140              | PVC           | Grey   |  |
| 8050               | PVC           | Black  |  |
| 8280               | PVC           | Black  |  |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/png-m0-8nl-ln.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/png-m0-8nl-ln.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.