



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

**Coax triax mixed en**

Nb of contacts Coax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Panel Drill Hole	M16
Jacket cable outside diameter [mm]	5.10 - 5.50 mm
Size	1E
Suggested matching part	<a href="#">FFA.1E.250.CTAC55Z</a>
Series	E - Outdoor Stepped Insert

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Solder
Insert configuration value	1E.250 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	12 A
Impedance	50 Ohms
VSWR	1.01 + 0.23 * f/GHz
Vtest	3000 V (AC), 4200 V (DC)
Cable type	RG 178 B/U, RG 196 A/U, RG 188 A/U, RG 316 B/U, RG 174 A/U, HF-2114, RG 122 /U
Bucket Dia.	1 mm (0.039in)
Contact Dia.	0.9 mm (0.035in)

## Form & Material

Shell style / Model id	PSA - Fixed receptacle, nut fixing, cable collet
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Variant	Nut for fitting a bend relief
Panel Drill Hole	M16


## Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	5.10 - 5.50 mm

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S2</b>	<b>S3</b>
mm.	20	21.5	M16x1.0	9	45	4.5	14.5	9	19
in.	0.79	0.85		0.35	1.77	0.18	0.57	0.35	0.75

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-250-ctlc55z.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-250-ctlc55z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

Compatible cap [BRE.1K.200.NAS](#)

## Cables

Cable PartNumber	Material	Colour	Cable image
CCX.50.080.297538N	PVC	Black	

[https://www.lemo.com/int\\_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-250-ctlc55z.html](https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/psa-1e-250-ctlc55z.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.