

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[BKT series](#)

Number of contacts Low Voltage	4
Gender	Reverse Gender
Locking system	Push-pull
Size	0B
Series	B - Indoor keyed

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/rgj-0b-304-cll.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/rgj-0b-304-cll.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	4
Insert configuration value	0B.304 - 4 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 A
Vtest (contact-contact)	1.2 kV (DC)
Vtest (contact-shell)	1 kV (DC)
Contact Dia.	0.7 mm (0.03in)
Number of differentiated pairs (High speed)	1
Gender	Reverse Gender

## Form & Material

Shell style / Model id	RG - Fixed coupler, nut fixing, key (G) at the flange end and keys (G,J or M) at the other end
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Front side: 1 key (alpha=0, female) , Other side: 2 keys (gamma=45, male)
Colour	Grey
Weight	11.49 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/rjg-0b-304-cll.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/rjg-0b-304-cll.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>Lmax</b>	<b>M</b>	<b>S1</b>	<b>S3</b>
mm.	12	13.8	M10x0.75	8	43	2	9	12
in.	0.47	0.54		0.31	1.69	0.08	0.35	0.47

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/rj1-0b-304-cl1.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/rj1-0b-304-cl1.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.