


Special



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

00and01Coaxial en

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Series	00 - NIM-CAMAC

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/rma-00-250-ntm.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/rma-00-250-ntm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Footprint IPC Class3 compatibility	No
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
VSWR	1.09 + 0.11 * f/GHz
Vtest	2100 V (AC), 3000 V (DC)
Contact retention	18 N
Contact Dia.	0.7 mm (0.03in)

## Form & Material

Shell style / Model id	RMA - Free coupler
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	2.51 g


## Environment

Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +260°C (max. temperature valid for short periods of use.)
F ret (min)	100 N
Salt Spray Corrosion	>144 hr

# Drawings

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/rma-00-250-ntm.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/rma-00-250-ntm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



## Dimensions

	<b>A</b>	<b>L</b>
mm.	6.5	22
in.	0.26	0.87

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/rma-00-250-ntm.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/rma-00-250-ntm.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.