

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[REDEL SP series en](#)

[Customer Drawing](#)

Number of contacts Low Voltage	1
Wire Size/AWG	32 - 28
Size	SP
Series	REDEL SP - Inner Push-Pull

Technical details

Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.5
Wire Size/AWG	32 - 28

Form & Material

Shell style / Model id	SAN - Male crimp contact for REDEL SP series, standard barrel
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.05 g

Environment

Technical domain	Medical
Environmental sealing (IP rating)	No IP rating

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Recommended By Lemo

Tools

Positionner	SOE.050.VC
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-505-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.