

[Standard](#)

Image for illustrative purpose only

Summary

[Request a quote](#)[REDEL SP series en](#)[Industry Brochure Medical](#)

Number of contacts Low Voltage	1
Wire Size/AWG	24 - 20
Size	SP
Series	REDEL SP - Inner Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-sp-inner-push-pull/san-535-zzc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	1
Contact Termination Low voltage	Crimp
Contact Dia.	0.9
Wire Size/AWG	24 - 20

Form & Material

Shell style / Model id	SAN - Male crimp contact for REDEL SP series, standard barrel
Housing material	Gold plated [ISO 27874] brass
Keying	No keying
Weight	0.18 g


Environment

Technical domain	Medical
Environmental sealing (IP rating)	No IP rating

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

Drawings



No keying

Dimensions

	A	C
mm.	0.9	1.1
in.	0.04	0.04

Recommended By Lemo

Tools	
Positionner	SOE.090.VC
Crimp tool	DPC.91.701.V