

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[REDEL SP series en](#)

[Customer Drawing](#)

Number of contacts Low Voltage	16
Wire Size/AWG	32 - 28
Gender	Reverse Gender
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	6.60 - 7.50 mm
Size	SP
Series	REDEL SP - Inner Push-Pull

https://www.lemo.com/int_en/catalog/product/view/id/538332/s/sas-m16-glm-7nz/category/50/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	16
Contact Termination Low voltage	Crimp
R (max)	8.5 mOhm
Insert configuration value	SP.M16 - 16 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	3 A
Test voltage contact-contact	1.88 (kV DC)
Max. Conductor	0.09 mm ² (AWG 28)
Min. Conductor	0.035 mm ² (AWG 32)
Air clearance	0.8 mm
Creepage distance	0.8 mm
Bucket Dia.	0.45 mm (0.0177in)
Contact Dia.	0.5 mm (0.0196in)
Wire Size/AWG	32 - 28
Gender	Reverse Gender

Form & Material

Shell style / Model id	SA/Z - Straight plug, key (N) or keys (P, S and T), with cable collet and nut for fitting a bend relief
Plug	Straight
Housing material	Proprietary sulfone, grey
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=50, plug: female contacts, receptacle: male contacts)
Colour	Grey - Black
Variant	Black collet nut for bend relief
Weight	6.83 g

https://www.lemo.com/int_en/catalog/product/view/id/538332/s/sas-m16-glm-7nz/category/50/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

Cable fixation

Cable termination protection	For cable bend relief
Fixation type	Cable collet
Jacket cable outside diameter [mm]	6.60 - 7.50 mm

Recommended By Lemo

Tools

Positionner	SOE.050.VM
Crimp tool	DPC.91.701.V

CAD

Documents

Eplan	Download
-------	--------------------------

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.16.T28.070NNZZ			

https://www.lemo.com/int_en/catalog/product/view/id/538332/s/sas-m16-glm-7nz/category/50/

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.