

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Series	00 - NIM-CAMAC

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/swh-00-250-clmv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	4 A
Impedance	50 Ohms
VSWR	1.09 + 0.11 * f/GHz
Vtest	2100 V (AC), 3000 V (DC)
Contact retention	18 N
Contact Dia.	0.7 mm (0.03in)

Form & Material

Shell style / Model id	SWH - Fixed coupler, nut fixing, watertight or vacuum-tight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	4.98 g


Environment

Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-20°C / +100°C
F ret (min)	100 N
Salt Spray Corrosion	>1000 hr

Drawings

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/swh-00-250-clmv.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	A	B	C	D	e	E	S1
mm.	24.5	11.0	10.2	1.5	M7x0.5	5.5	9
in.	0.96	0.43	0.4	0.06		0.22	0.35

Recommended By Lemo

Accessories

Compatible cap

[BRE.00.200.NAS](#)