

Customer Information Sheet

DRAWING No.: G125-FCXXX68L0-XXXXL



IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



DIMENSION	MEASUREMENT
DIM 'A'	(TOTAL No. OF CONTACTS - 2) x 0.625 + 3.80
DIM 'B'	(TOTAL No. OF CONTACTS - 2) x 0.625
DIM 'F'	(TOTAL No. OF CONTACTS - 2) x 0.625 + 1.80
EXAMPLE PART No. 10 CONTACT CONNECTOR WITH 150mm OF 26AWG WIRE = G125-MC11068L0-0150L 26 CONTACT CONNECTOR WITH 450mm OF 30AWG WIRE = G125-MC32668L0-0450L	

CONTACT No.	WIRE COLOUR
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GREY
10	WHITE


WIRE COLOURS REPEAT IN ABOVE ORDER FOR CONNECTOR ASSEMBLIES OVER 10 CONTACTS.

NOTES:

1. CABLE ASSEMBLIES WILL BE BULK PACKED IN BAGS.
2. FOR COMPLETE SPECIFICATION SEE COMPONENT SPECIFICATIONS C049XX AND C125XX (LATEST ISSUES).
3. CUSTOM LENGTH CABLE ASSEMBLIES CAN BE PRODUCED FROM 60mm TO 9999mm.



PATENTED TECHNOLOGY



ORDER CODE:

G125-FCXXX68L0-XXXXL

26 AWG = 1
28 AWG = 2
30 AWG = 3

DIM 'C' LENGTH:
0060 = 60mm MIN
9999 = 9999mm MAX

TOTAL No. OF CONTACTS:
06, 10, 12, 16,
20, 26, 34, 50

RTP	2	11.03.21	30101
NAME	ISS.	DATE	CN/CO
APPROVED:	R. PORTLOCK		
CHECKED:	R. ALEXANDER		
DRAWN:	R. PORTLOCK		
CUSTOMER REF.:			
ASSEMBLY DRG.:			