


Polar Cable

[Click here](#) for the 3D model.

General Information

Series	C28
Dielectric	Film/Foil Polypropylene
Style	Can
Description	Plastic Case and Cover, Ultra Sonically Welded Seal
Features	Ultra Sonically Welded Seal, Safety Class S3, UL_94 VO Disk
RoHS	Yes
Termination	Tin Copper
Lead	Cables
Qualifications	UL, VDE, UL (Construction Only), UL_94 VO Disk
AEC-Q200	No
Typical Component Weight	27 g

Dimensions

D	25mm +1mm
L	55mm +/-2mm

Specifications

Capacitance	3 uF
Tolerance	5%
Voltage AC	470 VAC
Temperature Range	-25/+85°C
Rated Temperature	85°C
Max dV/dt	20 V/us

Packaging Specifications

Terminal Type	Bolt-M8x12
Packaging	Bulk, Bag
Packaging Quantity	162

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.