





	A	REVISIONS	BY	CHKD	DATE	A	COUNT	REVISIONS	BY	CHKD	DATE
	△			.	.		△				.
	△				.		△				.
	△				.		△				.



No. of Pin	Part. No.	A	B
4	DF11-4DP-2DSA(01)	6.0	2.0
6	DF11-6DP-2DSA(01)	8.0	4.0
8	DF11-8DP-2DSA(01)	10.0	6.0
10	DF11-10DP-2DSA(01)	12.0	8.0
12	DF11-12DP-2DSA(01)	14.0	10.0
14	DF11-14DP-2DSA(01)	16.0	12.0
16	DF11-16DP-2DSA(01)	18.0	14.0
18	DF11-18DP-2DSA(01)	20.0	16.0
20	DF11-20DP-2DSA(01)	22.0	18.0
22	DF11-22DP-2DSA(01)	24.0	20.0
24	DF11-24DP-2DSA(01)	26.0	22.0
26	DF11-26DP-2DSA(01)	28.0	24.0
28	DF11-28DP-2DSA(01)	30.0	26.0
30	DF11-30DP-2DSA(01)	32.0	28.0
32	DF11-32DP-2DSA(01)	34.0	30.0

Notes: The minimum ordering quantity for header is one package(containing 100 pieces).

2: Insuiator : Nylon resin , Black

Contact Material: Brass

Contact Plating : $0.2\text{ }\mu\text{m}$ gold plating

No.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
APPROVED		<i>14/4 manufacture</i>	GENERAL DIMENSION		
REVIEWED		.	TOLERANCE		
CHECKED		.	6 or less		
DESIGNED			over 6 to 18		
DRAWN			over 18 to 50		
			over 50 to 125		
			over 125 to 250		
			ANGULAR		
DRAWING No.			SCALE		
EDC3-162393-01			UNITS		
			mm		
			5 : 1		