







Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




Recommended pattern




Recommend metal mask
Thickness : 0.15 to 0.2mm
Opening ratio : 100%

Mated connectors



Notes 1. Lead co-planarity include reinforced metal fittings shall be 0.1mm MAX.

			5	Polyester	Clear(Cover tape)			
2	Brass	Surface:Tin plated 1#m MIN	4	PS	Clear(Embossed carrier tape)			
		(Under plating)Copper plated 0.5#m MIN	3	Brass	Surface:Tin plated 1#m MIN			
1	Polyamide	Natural(Beige)・UL94V-0			(Under plating)Nickel plated 1#m MIN			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
								
 HIROSE ELECTRIC CO., LTD.		APPROVED	・HS. OKAWA	17.06.29	DRAWING NO.	EDC-367247-21-00		
		CHECKED	・TS. FUKUSHIMA	17.06.29	PART NO.	DF3EA-2P-2H(21)		
		DESIGNED	・TO. KUROMATSU	17.06.29	CODE NO.	CL543-0329-0-21		
		DRAWN	・TO. KUROMATSU	17.06.29	 1/2			

Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

