


Oct.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


2 Style and Dimension of Reel




Detail of part No. Label









HRS DRAWING FOR REFERENCE

Note 1. 1RL:800 Contacts.
2 Style of reelshows in figure.
3. Please make sure to check ths form of crimping using a cable in adusting an applicator.
4. Applicable cable is 10-12 AWG.
5. Refer to the technical specification (ETAP-H0824-00) for the packing type.
6. Please refer to the technical specification (ETAD-H0654-00, ETAD-H0653-00, ETAD-H1042-00) for handling.

NO.	MATERIAL	FINISH , REMARKS
1	Copper alloy	Contact area : Au plating 0.2μm min Wire barrel area : Sn plating 1 μm min Under plating : Ni plating 1 μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2:1	3	1	DIS-H-00022959	SN.MIWA	TT.OHSAKO	2025.04.08

HIROSE ELECTRIC CO.,LTD.

APPROVED	SJ.OKAMURA	2023.10.19
CHECKED	TT.OHSAKO	2023.10.19
DESIGNED	KT.NUMATA	2023.10.18
DRAWN	SK.CHIBA	2023.10.18

DRAWING NO.	EDC-402623-00-00
PART NO.	DF60S-1012SCFA
CODE NO.	CL0680-3082-0-00

3 1/1