




COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE




PART NO.	PRODUCT CODE	(A)	(B)	(C)	(D)	(E)
DX30M-14-CV(10)	CL230-5051-7-10	6.30	5.75	17.09	11.50	25.79
DX30M-20-CV(10)	CL230-5052-0-10	6.70	7.25	20.90	14.50	29.60
DX30M-26-CV(10)	CL230-5053-2-10	7.10	7.25	24.80	15.00	33.50
DX30M-36-CV(10)	CL230-5054-5-10	8.10	7.25	31.06	15.75	39.80
DX30M-50-CV(10)	CL230-5055-8-10	8.70	7.25	39.95	16.00	48.70
DX30M-68-CV(10)	CL230-5056-0-10	2	2	51.38	17.57	60.13

2 TOP VIEW OF DX30M-68-CV (1:1)



NOTE 1 COMPONENTS OF REF. NO. ①②③ AND ⑤ ARE APPENDED.



2	STAINLESS STEEL	5	POLYCARBONATE (LIGHT BEIGE)	UL94V-2
1	STAINLESS STEEL	4	POLYCARBONATE (LIGHT BEIGE)	UL94V-2
		3	STAINLESS STEEL	

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)			DESIGNED	CHECKED	APPROVED
			Y. Enami	Y. Enami	H. Murao
			02.4.8	02.4.8	02.04.09

DRAWING NO.	EDC3-123778-01	PART NO.	DX30M-**-CV(10)
SCALE	2 : 1	CODE NO.	

UNITS	mm	CL230	1
-------	----	-------	---