


Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES) 1. PARTS ①⑧⑨ ARE DELIVERED ASSEMBLED.
 PARTS ②③④⑤⑥⑦ ARE DELIVERED DISASSEMBLED.
 2. OUTER DIAMETER OF APPLICABLE CABLE IS $\phi 6.2 \pm 0.3$.
 3. DIMENSIONS IN PARENTHESES ARE SHOWN AS REFERENCES.

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
4	STEEL	SURFACE PLATING : NICKEL 3 μ m MIN. UNDER PLATING : COPPER 2 μ m MIN.	9	STAINLESS STEEL	
3	STEEL	SURFACE PLATING : NICKEL 3 μ m MIN. UNDER PLATING : COPPER 2 μ m MIN.	8	STEEL	SURFACE PLATING : NICKEL 2 μ m MIN. UNDER PLATING : COPPER 1 μ m MIN.
2	POLYCARBONATE	(GRAY), UL94V-0	7	BRASS	
1	POLYCARBONATE	(GRAY), UL94V-0	6	BRASS	
			5	STEEL	NICKEL PLATING : 3 μ m MIN.

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△				
HIROSE ELECTRIC CO., LTD.			APPROVED : YH. ENAMI 09.12.17	DRAWING NO. EDC3-120648-01		
			CHECKED : HO. MIWA 09.12.17	PART NO. FI-20-CV7		
			DESIGNED : HN. ANDO 09.12.17	CODE NO. CL230-0525-2-00		
			DRAWN : HN. ANDO 09.12.17	△ 1/1		