


Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	DIS-E-000115	T.Ito	Y.E	05.06.06					

NOTES: 1 APPLICABLE CABLE

	WIRE	INSULATOR OUTER DIAMETER 0.90 TO 1.00 DIA. CONDUCTOR SIZE (STRANDED) AWG26~27 OR EQUIVALENT
	VINYL SEATH OUTER DIAMETER	φ 5.0 * (1)
	DRAIN WIRE	AWG 25 OR EQUIVALENT 7/0.18 DIA. * (2)

- \* (1) CABLE ENTRY IS 5.6 MIN.
- \* (2) CONSTRUCTION IS FOR REFERENCE.



- 2 ADAPTER SHALL BE USED TO ALIGN INDIVIDUAL WIRE.
- 3 THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

2	PHOSPHOR BRONZE	GOLD PLATING	5	POLYCARBONATE	MEDIUM GRAY
4	POLYCARBONATE	TRANSPARENCY	4	POLYCARBONATE	TRANSPARENCY
1	POLYCARBONATE	TRANSPARENCY	3	BRASS	TIN PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED
		H. Tanaka	H. Tanaka	T. Watanabe	K. Miwa
		99.5.18	99.5.18	99.5.18	99.5.18
DRAWING NO. EDC3-120679-02			PART NO. TM11AP-88P (02)		
SCALE 4 : 1			CODE NO. CL222-2780-6-02		
UNITS mm			1/1		

TO
Q2