



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought




TE Part #216604-3
HV190 REC ASSY 2X 3P.




TE Part #3-794678-6
06P MICRO MNL ASSY,R/A,THRU,LF




TE Part #4-794678-6
16P MICRO MNL ASSY,R/A,THRU,LF




TE Part #2-1445096-6
MICRO MNL HDR ASSY SINGLE ROW




TE Part #1571636-4
TACT,SMT,GULL WING,100GF,T&R




TE Part #1-1879270-0
RP 2A 52R3 0.1% 15PPM CUT LENGTH




TE Part #3-2176263-6
RN 0402 56K2 0.1% 10PPM 5K RL



TE Part #1-5535512-7
14 MODII HORZ DR CE EESS .100



TE Part #5-435166-3
7000 DIP SW 8 POSN SEALED



TE Part #2-2176369-1
RQ 0603 64R9 0.1% 10PPM 5K RL

Documents

CAD Files

Customer View Model

[ENG_CVM_1393776-9_S00E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1393776-9_S00E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1393776-9_S00E.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Definitions General Purpose Relays

English

