




AMP

TE Internal #: 1901002-1

Premium Crimp Tooling, Removable/Interchangeable, MIL Spec /
TE Product Specification (114-), TE Certification, Battery, Hand
Crimping Tools

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes**

Power Technology Type: **Battery**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes
Power Technology Type	Battery
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 2-321598-4 TERMINAL 6 SOLIS RING 1/4	 TE Part # 323172 TERM, STRAT, SOLIS, RT, HR, 6, 3/8	 TE Part # 31811 TERMINAL, SOLIS R 4 1/4	 TE Part # 323171 TERMINAL, SOLIS R HR 6 5/16
 TE Part # 323175 TERMINAL, SOLIS R HR 4 3/8	 TE Part # 31812 TERMINAL, SOLIS R 4 3/8	 TE Part # 321598 TERMINAL, SOLIS R 6 1/4	 TE Part # 36810 TERMINAL, SOLIS R 6 3/4
 TE Part # 33467 TERMINAL, SOLIS R 6 3/8	 TE Part # 34319 SPLICE, SOLIS PARA 6	 TE Part # 33464 TERMINAL, SOLIS R 6 10	 TE Part # 36808 TERMINAL, SOLIS R 6 1/2



TE Part # 324309-2
TERM, SPLC, BUTT, STRAT, SOLIS, HR, 6



TE Part # 321298
TERMINAL,SOLIS R 6 10



TE Part # 1901000-1
NEST #6



TE Part # 8-52197-2
TERMINAL,SOLIS R 6 10



TE Part # 2-324309-2
SPLICE,SOLIS BUTT 6



TE Part # 2-33466-1
SOLISTRAND RING 6 5/16



TE Part # 33466
TERMINAL,SOLIS R 6 5/16



TE Part # 323174
TERMINAL,SOLIS R HR 4 5/16

Customers Also Bought



TE Part #ZPF000000000024114
901-20 R 27-13 PN 88



TE Part #582527-000
D-600-0125




TE Part #ZPF000000000004586
901-20 B 27




TE Part #ZPF000000000004591
901-20 B 61



TE Part #ZPF000000000004583
901-20 B 19



TE Part #52075-1
FLAG RELAY, SPECIAL-RR 12-10



TE Part #102100-2
MOD I RECP PLTD 30 SEL



TE Part #207654-1
KEYING PLUG



TE Part #500001-1
SPIRAP 1/4" PE, NAT, 50 FT



TE Part #1-2823588-3
M12 D-90 DEGREE-M-4, CAT 5E 8.4 MM, TE

Document



Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English