




AMP

TE Internal #: 58603-2
Commercial Crimp Tooling, Operator Releasable & Adjustable,
Removable/Interchangeable, TE Product Specification (114-), Hand
Crimping Tools
[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (2% in 4745822) Article Safe Usage Statements:





Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-963745-3 TAB 2,8X0,8	 TE Part # CAT-T4827-T273 TIMER, RECEPTACLE AND TAB	 TE Part # 2-963745-1 SPECIAL TERMINAL 20-17 AWG PTPB LP	 TE Part # 2-962842-3 TAB 2.8x0.8 CONTACT CF SRC Au LP
 TE Part # 2-962842-2 TAB 2.8x0.8 CONTACT CF SRC Ag	 TE Part # 1-963745-1 SPECIAL TERMINAL 20-17 AWG PTPB LP	 TE Part # 927777-6 JUNIOR POWER TIMER CONTACT	 TE Part # 8-962841-3 TAB 2.8x0.8 CONTACT SRC
 TE Part # 8-962841-1 TAB 2.8x0.8 CONTACT SRC	 TE Part # 6-962841-6 TAB 2.8x0.8 CONTACT SRC	 TE Part # 1-963745-2 SPECIAL TERMINAL 20-17 AWG SLIPB LP	 TE Part # 6-962841-7 TAB 2.8x0.8 CONTACT SRC



TE Part # 1-963746-2
SPECIAL TERMINAL 17-13 AWG
SLIPBR LP

TE Part # 927779-6
JPT REC 2.8 Contact SRC Ag (LP)

TE Part # 8-962842-1
TAB 2.8x0.8 CONTACT SRC

TE Part # 1-963746-1
SPECIAL TERMINAL 17-13 AWG PTPB
LP

TE Part # 2-962841-3
TAB 2.8x0.8 CONTACT CF SRC Sn

TE Part # 927777-3
JUNIOR POWER TIMER CONTACT

Customers Also Bought

TE Part #CAT-T4827-CH8172
Timer Connector Housing

TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB

TE Part #CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB

TE Part #1-968977-9
2,8MM FLA-STE-GEH3P

TE Part #6-1393292-3
V23074A2002A403-EV-CBOX

Documents

- Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Bottoming Dies

English
- Instruction Sheets

Instruction Sheet (U.S.)

English



PRO-CRIMPER II Hand Tool Assembly 58603-1 w/Die Assembly 58603-2

English

Instruction Sheet (U.S.)

English