




Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (108-), UL/CSA**
TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (108-), UL/CSA
TE Certification	Yes – Certificate Included
Power Technology Type	Manual, Pneumatic
Tooling Type	Tetra Crimp / Platform Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2-520181-2 ULTRA-FAST 187 ASY REC 22-18 AWG TPBR	 TE Part # 2-521144-2 ULTRA-FAST 250 ASY TAB 22-18 TPBR	 TE Part # 2-521192-2 ULTRA-FAST 250 ASY REC 22-18 TPBR	 TE Part # 2-521102-2 ULTRA-FAST 187 ASY Tab 22-18 TPBR
 TE Part # 2-521406-2 205 ULTRA-FAST RCPT 22-18 TPBR	 TE Part # 2-520306-2 ULTRA-FAST .110/.125 ASY REC 22-18 TPBR	 TE Part # 2-520856-2 ULTRA-FAST 250 ASY REC 22-18 TPBR	 TE Part # 2-521164-2 205 ULTRA-FAST ASY REC FLAG 22-18 TPBR
 TE Part # 2-521103-2 ULTRA-FAST 187 ASY REC 22-18 TPBR	 TE Part # 2-520310-2 ULTRA-FAST .110/.125 ASY REC 22-18 TPBR	 TE Part # 2-520103-2 ULTRA-FAST 250 ASSEMBLY TAB 22-18 AWG BR	 TE Part # 2-520183-2 ULTRA-FAST 250 ASY REC 22-18 TPBR







TE Part # 2-520102-1
ULTRA-FAST 250 ASSEMBLY TAB 22-18 AWG BR



TE Part # 2-520129-2
ULTRAFAST 250 ASSY FLAG 22-18 TPBR LP



TE Part # 2-521104-2
ULTRA-FAST 187 ASY REC 22-18 TPBR




TE Part # 2-520182-2
ULTRAFAST 187 ASSY REC 22-18 TPBR LP




TE Part # 5-520183-2
ULTRA-FAST 250 ASY REC 22-18 AWG TPBR



TE Part # 9-520261-2
ULTRA-FAST 187 ASY REC 22-18 AWG TPBR



TE Part # 2-520102-2
ULTRA-FAST 250 ASSEMBLY TAB 22-18 AWG BR



TE Part # 2-520335-2
ULTRA-FAST 187 ASY REC 22-18 TPBR


Customers Also Bought



TE Part #994057-000
AD-1494-723-SLTC-HLD-ASY



TE Part #58080-3
DIES U-FAST + FASTON 16-14 DIE SET



TE Part #58628-2
PROCRMP DIESET 26-14 ULTRAFAST



TE Part #323291
TERMINAL,SOLIS R 2 1/2




TE Part #1423160-3
7014AC=RLY,STD,ON,4P,120VAC,20




TE Part #1423162-2
7022AB=RLY,STD,OFF,2P,120VAC,5



TE Part #1976924-1
TOOL, PLIERS, QUADRAX



TE Part #3-21053-2
O RING



TE Part #91156-2
EXTRACTION TOOL



TE Part #1123721-3
ECONOMY POWER REC CONT

Documents



Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English