



All HW High Tack White Polyester Labels (44)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER




TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER

Customers Also Bought



TE Part #NB-PTCO-192
Pt1000, 1.2x4.0, Class A, PTFM102A1A0



TE Part #CV25894001
RW-175-E-1/2-X-SP



TE Part #F07599-000
MP-508254-5-8A



TE Part #2-1879026-6
YR1 0.1% 17R8




TE Part #9-1879221-7
CPF 0603 16R9 0.1% 25PPM 1K RL



TE Part #1-1879222-5
CPF 0603 26R7 0.1% 25PPM 1K RL



TE Part #1-1879222-7
CPF 0603 28R 0.1% 25PPM 1K RL



TE Part #6-2213772-7
AV22 DPL 3A MOVE RING LED RED 24V



TE Part #5-6437630-2
FTN7904=FLAT TOGGLE



TE Part #5-6437630-4
FTD79G04=FLAT TOGGLE

Documents

Product Drawings

HW-445445-2-9

English

Datasheets & Catalog Pages

HW High Tack White Polyester labels

English

IDENTIFICATION SELECTION GUIDE

English



Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English