



REVISIONS					
変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E4	REVISED	ECR-17-010634	21JUL2017	TS HY



- 注
- 1. 嵌合相手端子型番 ; 171631
 - ② 部分金めっき 0.38 μm 最小
 - ③ 部分金めっき 1.27 μm 最小
 - ④ 部分半田めっき 2.0 μm 最小
 - 5. 一般公差 : 10以下 ±0.2 10以上30以下 ±0.25 30以上100以下 ±0.3 角度 ±3°

- NOTE ;
- 1. TAB CONTACT ; 171631
 - ② SELECTIVE GOLD PLATING 0.38 μm MIN.
 - ③ SELECTIVE GOLD 1.27 μm MIN.
 - ④ SELECTIVE TIN-LEAD PLATING 2.0 μm MIN.
 - 5. TOLERANCES UNLESS OTHERWISE SPECIFIED.
10MAX : ±0.2 10-30 : ±0.25 30-100 : ±0.3 ANGLES : ±3°



OBSOLETE	SELECTIVE GOLD PLATING 部分金めっき ③ ④	PHOS-BRONZE t = 0.3 リン青銅 板厚 0.3	171630-6
	SELECTIVE GOLD PLATING 部分金めっき ②	PHOS-BRONZE t = 0.3 リン青銅 板厚 0.3	171630-5
	PRE-TIN 錫めっき済 (0.76 μm MIN.)	PHOS-BRONZE t = 0.3 リン青銅 板厚 0.3	171630-2
	PRE-TIN 錫めっき済 (0.76 μm MIN.)	BRASS t = 0.3 黄銅 板厚 0.3	171630-1
	FINISH 仕上	MATERIAL 材 料	PART NUMBER 型 番

適合電線断面積 (WIRE RENG)	被覆外径 (INSULATION DIA)
AVS 0.2-0.5mm ² (AWG24-20)	1.4-2.4mmφ

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

±

MATERIAL
材料

SEE TABLE

FINISH
仕上

SEE TABLE

DWN
D.MATSUURA
24OCT07

CHK
T.KOHNO
24OCT07

APVD
Y.FUJIWARA
24OCT07

PRODUCT SPEC
製品規格
108-5262

APPLICATION SPEC
取付適用規格
114-5082

WEIGHT
0.35 g

TE Connectivity

NAME
名称

—

ECONOSEAL J MK-II CONN RECEPTACLE CONTACT

—

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-171630

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
尺度 5:1

SHEET
1 OF 1

REV
E4

1470-19 (1/15)