


PART NO.	SIZE		RECOMMENDED STRIP LENGTH	MINIMUM PULL-OUT STRENGTH SLEEVE STRAND CONDUCTOR	COLOUR	d ₁	△ ₃ d ₂	L ₁	L ₂	s ₁	s ₂	COLOR TYPE	PACKAGE QTY
	mm ²	AWG	ABISOLIER-LÄNGE	MINDEST-AUSZUGSKRAFT HÜLSE LITZENLEITER	FARBE								VERPACKUNGSEINHEIT
BESTELL-NR.			/mm	/N	△ ₄	/mm	/mm	/mm	/mm	/mm	/mm	△ ₄	PARTS/STÜCK BAG/BEUTEL
966 067-1	0.50	20	8.5+0.2	20	WHITE WEIß	1.0 +0.14	2.6 ±0.2	12.0 ±1.5	6.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
966 067-2	0.50	20	10.5+0.2	20	WHITE WEIß	1.0 +0.14	2.6 ±0.2	14.0 ±1.5	8.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
966 067-3	0.50	20	12.5+0.2	20	WHITE WEIß	1.0 +0.14	2.6 ±0.2	16.0 ±1.5	10.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
966 067-4	0.75	18	8.5+0.2	30	GREY GRAU	1.2 +0.14	2.8 ±0.2	12.0 ±1.5	6.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN	500
966 067-5	0.75	18	10.5+0.2	30	GREY GRAU	1.2 +0.14	2.8 ±0.2	14.0 ±1.5	8.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN	500
966 067-6	0.75	18	12.5+0.2	30	GREY GRAU	1.2 +0.14	2.8 ±0.2	16.0 ±1.5	10.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN	500
966 067-7	0.75	18	14.5+0.2	30	GREY GRAU	1.2 +0.14	2.8 ±0.2	18.0 ±1.5	12.0 ±0.6	0.15 ±0.05	0.25 ±0.10	DIN	500
966 067-8	1.00	18	8.5+0.2	35	RED ROT	1.4 +0.14	3.0 ±0.2	12.0 ±1.5	6.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
966 067-9	1.00	18	10.5+0.2	35	RED ROT	1.4 +0.14	3.0 ±0.2	14.0 ±1.5	8.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-0	1.00	18	12.5+0.2	35	RED ROT	1.4 +0.14	3.0 ±0.2	16.0 ±1.5	10.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-1	1.00	18	14.5+0.2	35	RED ROT	1.4 +0.14	3.0 ±0.2	18.0 ±1.5	12.0 ±0.6	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-2	1.50	16	10.5+0.2	40	BLACK SCHWARZ	1.7 +0.25	3.5 ±0.2	14.0 ±1.5	8.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-3	1.50	16	12.5+0.2	40	BLACK SCHWARZ	1.7 +0.25	3.5 ±0.2	16.0 ±1.5	10.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-4	1.50	16	14.5+0.2	40	BLACK SCHWARZ	1.7 +0.25	3.5 ±0.2	18.0 ±1.5	12.0 ±0.6	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-5	1.50	16	20.5+0.2	40	BLACK SCHWARZ	1.7 +0.25	3.5 ±0.2	24.0 ±2.0	18.0 ±0.6	0.15 ±0.05	0.25 ±0.10	DIN/1	500
1-966 067-6	2.50	14	10.5+0.2	50	BLUE BLAU	2.2 +0.25	4.2 ±0.2	14.0 ±1.5	8.0 ±0.4	0.15 ±0.05	0.25 ±0.10	DIN/2	500
1-966 067-7	2.50	14	14.5+0.2	50	BLUE BLAU	2.2 +0.25	4.2 ±0.2	18.0 ±1.5	12.0 ±0.6	0.15 ±0.05	0.25 ±0.10	DIN/2	500
1-966 067-8	2.50	14	20.5+0.2	50	BLUE BLAU	2.2 +0.25	4.2 ±0.2	24.0 ±2.0	18.0 ±0.6	0.15 ±0.05	0.25 ±0.10	DIN/2	500
1-966 067-9	4.00	12	12.5+0.2	60	GREY GRAU	2.8 +0.25	4.8 ±0.4	17.0 ±1.5	10.0 ±0.4	0.20 ±0.05	0.30 ±0.10	DIN/2	500
2-966 067-0	4.00	12	14.5+0.2	60	GREY GRAU	2.8 +0.25	4.8 ±0.4	20.0 ±1.5	12.0 ±0.6	0.20 ±0.05	0.30 ±0.10	DIN/2	500
2-966 067-1	4.00	12	20.5+0.2	60	GREY GRAU	2.8 +0.25	4.8 ±0.4	26.0 ±2.0	18.0 ±0.6	0.20 ±0.05	0.30 ±0.10	DIN/2	100
2-966 067-2	6.00	10	15.5+0.2	80	YELLOW GELB	3.5 +0.30	6.3 ±0.4	20.0 ±1.5	12.0 ±0.6	0.20 ±0.05	0.30 ±0.10	DIN	100
2-966 067-3	6.00	10	22.5+0.2	80	YELLOW GELB	3.5 +0.30	6.3 ±0.4	26.0 ±2.0	18.0 ±0.6	0.20 ±0.05	0.30 ±0.10	DIN	100
2-966 067-4	10.00	8	15.5+0.2	90	RED ROT	4.5 +0.30	7.6 ±0.4	22.0 ±2.0	12.0 ±0.6	0.20 ±0.05	0.40 ±0.15	DIN	100
2-966 067-5	10.00	8	22.5+0.2	90	RED ROT	4.5 +0.30	7.6 ±0.4	28.0 ±2.0	18.0 ±0.6	0.20 ±0.05	0.40 ±0.15	DIN	100
2-966 067-6	16.00	6	16.5+0.2	100	BLUE BLAU	5.8 +0.30	8.8 ±0.4	24.0 ±2.0	12.0 ±0.6	0.20 ±0.05	0.40 ±0.15	DIN	100
2-966 067-7	16.00	6	22.5+0.2	100	BLUE BLAU	5.8 +0.30	8.8 ±0.4	28.0 ±2.0	18.0 ±0.6	0.20 ±0.05	0.40 ±0.15	DIN	100

OBSOLETE



- △₁ THE AWG CROSS-SECTION CAN DIFFER SLIGHTLY FROM THE DIN-STANDARD CROSS-SECTION VALUES
- 2 NOTE DELETED
- △₃ MAX. INSULATION-DIA. OF WIRE: d₂ MIN.- 0.1
- △₄ PARTS PER DIN 46228 PART 4
COLOUR TYPE 1: COLOUR PER FRENCH STANDARD
COLOUR TYPE 2: COLOUR PER GERMAN STANDARD
COLOUR TYPE DIN: COLOUR PER DIN 46228 PART 4
5. NOTE DELETED
6. NOTE DELETED.
- △ 0.6MM ALLOWABLE MOLDING FLASH PRESENT IN THIS ZONE.
- △₈ PARTS PACKED IN PLASTIC BAG, LOOSE PIECE
- △₉ MATERIAL:
METAL SLEEVE – COPPER
PLASTIC SLEEVE – POLYPROPYLENE
- △₁₀ FINISH:
METAL SLEEVE – TIN PLATE 3µm MIN THICKNESS
PLASTIC SLEEVE COLOR – SEE TABLE
- 11 MAXIMUM RECOMMENDED TEMAPERATURE 105°C
- 12 CSA APPROVED, FILE 701553

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SCHMIDT 13NOV1996	TE Connectivity				
		CHK W.BoCK 13NOV1996					
DIMENSIONS: mm		APVD G. FELDMER 13NOV1996	NAME				
		PRODUCT SPEC	WIRE FERRULE WITH PLASTIC SLEEVE, SINGLE CONDUCTOR, DIN 46228 PART 4, LOOSE PIECE DIN, FRENCH- & GERMAN COLOR CODING				
		APPLICATION SPEC					
MATERIAL	FINISH	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=966067	RESTRICTED TO	
△ ₉	△ ₁₀	—	CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	REV B8