







REV
A
DRCP26-126S *

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
A	REVISED AND REDRAWN E.O. P20586	12-16-10	RDR



3D VIEWS



- NOTES:
1. ALL DIMENSIONS ARE INCHES [METRIC].
 2. DIMENSION TOLERANCE $\pm .025$ [0.64]
 3. MATERIAL SPECIFICATION:
HOUSING / BACKSHELL = PLASTIC (BLACK), TPA (GREY)
GROMMET / MAIN SEAL= RUBBER
BOLT = STEEL / ZINC PLATED
 4. PLUG MATING TORQUE = 44-62 in-lb [5-7 Nm].
 5. REFER TO 0425-015-0000 FOR CONTACT AND CRIMPING DETAILS.
 6. REQUIRES COVER (NOT INCLUDED) FOR HIGH PRESSURE SPRAY APPLICATIONS.
 7. SECURE HARNESS WITH TIE WRAPS FOR HIGH VIBRATION APPLICATIONS.
 8. SEE SHEET 2 FOR ALTERNATE KEYS. CONSULT FACTORY FOR KEY AVAILABILITY.
 9. THIS PART MATES WITH DRCP25-126P***-**** (** = KEY) (**** = MOD)
 10. TPA SHIPPED IN OPEN POSITION, CLOSE TO SECURE TERMINALS, REMOVE TO SERVICE.
 11. USE BLADE TYPE PROBE FOR TERMINAL PRESENCE CHECK.

SEALING RANGE		
CAVITY SIZE	MINIMUM	MAXIMUM
#20	.063" [1.6mm]	.124" [3.15mm]
#12	.118" [3.0mm]	.210" [5.3mm]

SIGNATURE & DATE	
DR	S. YU 10DEC10
CHK	C. WOODRUFF
PE	C. WOODRUFF
APPD	<i>[Signature]</i> 12/15/10
SCALE	NONE
WT	

PLUG
120 #20 + 6 #12
DRCP SERIES


ENVELOPE

EP	MATL. CODE
3850 INDUSTRIAL AVE. HEMET, CA 92545	
B	DRCP26-126S *
DWG SIZE	CODE 11139 SHEET 1 OF 2


REV
A
DRCP26-126S *

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
A	SEE SHEET -1-	12-16-10	RDR


DRCP26-126SA




DRCP26-126SC




DRCP26-126SE




DRCP26-126SB



DRCP26-126SD



DRCP26-126SF



NOTES: SEE SHEET -1-

SIGNATURE & DATE	
DR	
CHK	
PE	
APPD	
SCALE	NONE WT

PLUG
120 #20 + 6 #12
DRCP SERIES

ENVELOPE

EP	MATL. CODE
 3850 INDUSTRIAL AVE. HEMET, CA 92545	
DEUTSCH INDUSTRIAL	
B	DRCP26-126S *
DWG SIZE	CODE 11139 SHEET 2 OF 2