


	DESIGNED FOR USE WITH RG180/U	REVISIONS			
	CABLE ENTRY DIAMETER MINIMUM	REV	DESCRIPTION	DATE	APPROVED
	CONTACT .021	01 ₁	REDRAWN ON CAD ECN 94-0474	6/1/95	6/1/95
	HOUSING .106				
	FERRULE .153				
	HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303		GOLD PLATE PER MIL-G-45204	
	DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457		N/A	
	CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H		GOLD PLATE PER MIL-G-45204	
	RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H		N/A	
	GASKET	SILICONE RUBBER PER ZZ-R-765		N/A	
	SHRINK TUBING	HEAT SHRINKABLE POLYOLEFIN COMPOUND MIL-I-23053/4		N/A	
	FERRULE	SOFT COPPER ALLOY		GOLD PLATE PER MIL-G-45204	
	COMPONENT	MATERIAL		FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY B.M.	DATE 8/17/79	AMP M/A-COM M/A-COM a Division of AMP Incorporated 140 Fourth Avenue Waltham, MA 02154-7577		
	CHECKED BY R. SMITH	8/21/79			
	APPROVED BY G.H.	8/23/79			
	These drawings and specifications are the property of M/A-COM Interconnect Division and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OSM STRAIGHT CABLE PLUG SOLDER ATTACHMENT		
408-04964		SIZE B	CODE IDENT NO. 26805	2031-5156-29	REV 01 ₁
NO. AP. 20-080		SCALE 5:1		SHEET 1 OF 1	