





	1.500	1.100	1 1	24	1-103308-3
	3.300	2.900	29	60	1-103308-2
OBSOLETE	3.100	2.700	27	56	1-103308-1
	2.800	2.400	24	50	1-103308-0
OBSOLETE	2.500	2.100	21	44	103308-9
	2.300	1.900	19	40	103308-8
	2.000	1.600	16	34	103308-7
	1.600	1.200	12	26	103308-6
	1.300	.900	9	20	103308-5
OBSOLETE	1.200	.800	8	18	103308-4
	1.100	.700	7	16	103308-3
	1.000	.600	6	14	103308-2
	.800	.400	4	10	103308-1
	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
H. MOLL
CHK
L. MEYER
APVD
R. FEIDT

8-27-87
9-03-87
9-03-87

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL: GLASS FILLED NYLON
OR PBT, BLACK,
UL 94V-0 RATED
POSTS: BRASS

NAME
HEADER ASSY, LOW PROFILE,
AMP-LATCH

PRODUCT SPEC
108-40018

APPLICATION SPEC
-

SIZE
A1

CAGE CODE
00779

DRAWING NO
103308

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
M