



LOC	DIST	REVISIONS					
AJ	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REV PER ECO 08-010721	28JUL2008	DW	MS



<u>ELECTRICAL</u>		FREQUENCY NOMINAL IMPEDENCE VOLTAGE RATING VSWR (MATED CONNECTORS ONLY) INSULATION RESISTANCE DIELECTRIC WITHSTANDING VOLTAGE		DC — 6 GHz 50 OHMS 250 VOLTS (VRMS MAX) @ SEA LEVEL 1.20:1 MAX @ 2 GHz 1.40:1 MAX @ 6 GHz 1,000 MEGOHMS MIN @ 250VDC 500 VOLTS (VRMS MIN) @ SEA LEVEL	
<u>MECHANICAL</u>		CONNECTOR DURABILITY		100 MATING CYCLES	
<u>ENVIRONMENTAL</u>		TEMPERATURE RATING		-40°C(-40°F) TO +125°C(257°F)	
PRODUCT SPEC					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.WALLACE CHK M.STIMELING APVD M.STIMELING	28JUL2008 28JUL2008 28JUL2008	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 4 PLC ± - ANGLES ± 1°		NAME SSMT RIGHT ANGLE JACK TO JACK CABLE ASSEMBLY -	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A2	CAGE CODE 00779
MATERIAL -		FINISH -		DRAWING NO C=1064529	
		WEIGHT -		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 15:1	SHEET 1 OF 1
				REV C	

A