


© - TE Connectivity. All Rights Reserved.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	C1	REVISED PER ECR-25-260429	29OCT2025	SA MFP


<b>AMP</b> WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED




- 1 WIRE INSULATION DIAMETER Ø .105 TO Ø .200
- △2 MATERIAL:  
BODY - COPPER (QQ-C-576)  
INSULATION - PVC
- △3 FINISH:  
BODY - TIN PLATE PER ASTM B-545  
INSULATION COLOR - YELLOW

1	WIRE SPLICE	34135
QTY	PART NO	PART NO

<b>AMP INCORPORATED CUSTOMER SERVICE SYSTEMS</b>		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600 V MAX [1000 V FIXTURES AND SIGNS]
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm <sup>2</sup> [5,180-13,100]
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ± 1° ANGLES
MATERIAL	FINISH
△2	△3

DWN jr_ruth 05SEP03	 TE Connectivity	
CHK T MICHELUTTI 05SEP03	NAME WIRE SPLICE, PARALLEL, PLASTI-GRIP, WIRE SIZE: 12-10 AWG	
APVD T MICHELUTTI 05SEP03	PRODUCT SPEC UL 486C	RESTRICTED TO
APPLICATION SPEC 114-2161	SIZE A3	CAGE CODE 00779
WEIGHT	DRAWING NO C-34135	SCALE 4:1
CUSTOMER DRAWING	SHEET 1 OF 1	REV C1