


**Table 1: Dimensions** Millimeters (*Inches*)

Size	(A)	(B) Minimum	(L) Nominal	(C) Minimum	(D) Maximum	(W)
TC 4001	19.1(0.750) ± 1.6(0.063)	10.2(0.400)	3.8(0.15)	1.6(0.063)	0.8(0.030)	0.51(0.020) ± 0.1(0.005)
TC 4003	25.4(1.000) ± 1.6(0.063)	14(0.550)	3.8(0.15)	3.2(0.125)	1.3(0.050)	0.64(0.025) ± 0.1(0.005)
TC 4005	28.6(1.125) ± 1.6(0.063)	14(0.550)	3.8(0.15)	6.4(0.250)	2.5(0.100)	0.69(0.027) ± 0.1(0.005)

Color: TC4001 White
TC4003 Red
TC4005 Gray

Reference Specification TEC-108-120013

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2018 TE Connectivity

DIMENSIONS: mm		DWN J. Bitter	29-NOV-16	MATERIAL —		FINISH —	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK —	—	 TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD —	—				
		PRODUCT SPEC —		NAME TC-CAPS			
		APPLICATION SPEC —		SIZE A4	CAGE CODE 06090	DRAWING NO TC-CAPS	RESTRICTED TO —
		WEIGHT 0					
CUSTOMER DRAWING				SCALE None	SHEET 1 of 1	REV E	