

REVISION			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE OF CD PER ECO-19-013153	9/18/2019	I. MYONG



NOTES:

1. ONE-PART EPOXY FLEXIBLE ADHESIVE TAPE.
2. TEMPERATURE RANGE: -55°C TO $+200^{\circ}\text{C}$
3. TAPE IS SUPPLIED ON 100 FOOT REEL

3/4" WIDE X .020" THICK X 100FT

4. SPECIFICATIONS:

Raychem RT-1255
Raychem RT-1014

5. SDS DOCUMENTS:

RAY 3133

6. SHELF LIFE:

REFER TO TE SPEC SHEET No. 126-116006.

Raychem Harness & Components **CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. AND INCH DIMENSIONS ARE IN SHOWN IN (PARENTHESES).			 TE Connectivity				
DECIMALS: .000 ± 0.000 .00 ± 0.00 .0 ± 0.0		ANGLES: ± 0° 00'					
TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.			TITLE: TE/Raychem FLEXIBLE THERMOFIT ADHESIVE TAPE				
			DRAWING NO: S1255-04				
DRAWN: 21Jun2019 G.Rositano	APPROVED: 19JUL2019 I.Myong	CAGE CODE 06090	CAD FILE: S1124_cd	SIZE: A	SCALE: 	THIRD ANGLE PROJ. 	SHEET: 1_OF_1