


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Y	REVISED PER ECR-26-271876	26MAR2026	MA	JFS



- 1 PARTS PACKAGED UNASSEMBLED.
- 2 CABLE CLAMPING AREA ADJUSTABLE FROM .004 TO .055 SQ IN BY REVERSING CLAMPING INSERTS.
- 3 .329 MAXIMUM CABLE OUTSIDE DIAMETER.
- 4 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 800 ONLY.
- 5 OBSOLETE PART NUMBER.
- 6 STAINLESS STEEL (NON MAGNATIC).
- 7 CABLE CLAMP WITH NON-MAGNETIC STAINLESS STEEL SCREWS.
- 8 ZINC PLATED STEEL, NON-HEXAVALENT CHROMATE.

- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 10 SPECIAL PACKAGING CONSISTING OF 1 KIT PER INDIVIDUAL BAG, 20 INDIVIDUAL BAGS PER LARGER BAG, 5 LARGER BAGS PER SHIPPER BOX.

OBSOLETE	10	8	.50 [±] .00 _{-.05}	#5-20	2-206062-0
OBSOLETE	7 4 BULK	6	.50 [±] .00 _{-.05}	#5-20	1-206062-9
	4 BULK	8	.50 [±] .00 _{-.05}	#5-20	1-206062-7
	INDIVIDUAL	8	.38 [±] .00 _{-.05}	#5-20	1-206062-6
	4 BULK	8	.38 [±] .00 _{-.05}	#5-20	1-206062-5
	INDIVIDUAL	8	.50 [±] .00 _{-.05}	#5-20	1-206062-4
	INDIVIDUAL	8	.62 [±] .00 _{-.05}	#5-20	1-206062-3
	7 INDIVIDUAL	6	.50 [±] .00 _{-.05}	#5-20	1-206062-2
SUPERSEDED BY 1-206062-3	INDIVIDUAL	8	.62 [±] .00 _{-.05}	#5-20	1-206062-1
9 OBSOLETE	SMALL PACK	8	.38 [±] .00 _{-.05}	#5-20	1-206062-0
AMP BRAZIL USE ONLY	INDIVIDUAL		12mm [±] .0 _{-.8}	3mm-20	5 206062-9
AMP BRAZIL USE ONLY	INDIVIDUAL		10mm [±] .0 _{-.8}	3mm-20	5 206062-8
SUPERSEDED BY 1-206062-7	4 BULK	8	.50 [±] .00 _{-.05}	#5-20	206062-4
SUPERSEDED BY 1-206062-4	INDIVIDUAL	8	.50 [±] .00 _{-.05}	#5-20	206062-3
SUPERSEDED BY 1-206062-5	4 BULK	8	.38 [±] .00 _{-.05}	#5-20	206062-2
SUPERSEDED BY 1-206062-6	INDIVIDUAL	8	.38 [±] .00 _{-.05}	#5-20	206062-1
PACKAGING		SCREW FINISH	SCREW LENGTH	SCREW TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A GRAFF 4/29/91	TE Connectivity		
		CHK W.G.LENKER 7-22-92			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		
		0 PLC ± -	CABLE CLAMP KIT, STANDARD, SHELL SIZE 11, CPC		
		1 PLC ± -			
		2 PLC ± -	SIZE		
		3 PLC ± -			
		4 PLC ± -	CAGE CODE		
		ANGLES ± -			
MATERIAL		FINISH	DRAWING NO		
THERMOPLASTIC		-	RESTRICTED TO		
			A300779C-206062		
			CUSTOMER DRAWING		
			SCALE	SHEET	REV
			NTS	1 OF 1	Y