




LOC	DIST	REVISONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED PER ECO-12-013192	24AUG2012	BMM	MRS
			A1	RELEASED PER ECO-15-012866	17NOV2015	KQ	SH




A technical line drawing of a rectangular metal frame. The frame is composed of four L-shaped sections joined at the corners. Each corner joint features a small, rectangular protrusion or tab. The drawing is shown from an isometric perspective, highlighting the three-dimensional structure of the frame.



2169851-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17AUG2010 B. MATTHEWS CHK 17AUG2010 M. SCHMITT APVD 17AUG2010 M. SCHMITT		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±.1 2 PLC ±.1 3 PLC ±.1 4 PLC ±.1 ANGLES ±1° FINISH		NAME HEATSINK CLIP GANGED SFP+ -	
		PRODUCT SPEC 108-2364		SIZE A2	
MATERIAL 		APPLICATION SPEC 114-13120		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-2169851	
		Customer Drawing		SCALE 4:1 SHEET 1 OF 3 REV A1	

P/N: 2169851-6
UNMARKED DIMENSION SAME AS 2169851-1



2169851-6

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS CHK M. SCHMITT APVD M. SCHMITT	17AUG2010 17AUG2010 17AUG2010	 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±1°		NAME HEATSINK CLIP GANGED SFP+ -			
		PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120		SIZE A2		CAGE CODE 00779	
MATERIAL		WEIGHT -		DRAWING NO C-2169851		RESTRICTED TO -	
FINISH		Customer Drawing		SCALE 4:1		SHEET 2 OF 3	
						REV A1	


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT copyright.d0te-ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD

P/N:2169851-8
UNMARKED DIMENSION SAME AS 2169851-6



SCALE 10:1



2169851-8
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS CHK M. SCHMITT APVD M. SCHMITT	17AUG2010 17AUG2010 17AUG2010	TE Connectivity		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-2364		NAME HEATSINK CLIP GANGED SFP+		
	0 PLC ± 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1 4 PLC ±0.1 ANGLES ±1° FINISH	APPLICATION SPEC 114-13120	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-2169851
MATERIAL		Customer Drawing		SCALE 4:1	SHEET 3	OF 3 REV A1