

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	K	REVISED PER ECO-16-011204	29AUG2016	AP	DG

5,0 HEX

GROOVE TO INDICATE M3 INNER THREAD

1

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

1	OBSOLETE	10,8	4-40 UNC	4-40 UNC	6,0	TINPLATED	BRASS	3-829261-0
1	OBSOLETE	9,8	M3	4-40 UNC	5,0			2-829261-8
			4-40 UNC	M3	5,0			2-829261-6
			M3	M3	5,0			2-829261-4
			4-40 UNC	4-40 UNC	5,0			2-829261-2
1	OBSOLETE	19,0	M3	4-40 UNC	14,2	TINPLATED	BRASS	1-829261-8
			4-40 UNC	M3	14,2			1-829261-6
			M3	M3	14,2			1-829261-4
			4-40 UNC	4-40 UNC	14,2			1-829261-2
	OBSOLETE	12,7	M3	4-40 UNC	7,9			829261-8
			4-40 UNC	M3	7,9	829261-6		
			M3	M3	7,9	829261-4		
			4-40 UNC	4-40 UNC	7,9	829261-2		
		DIM "D"	DIM "C"	DIM "B"	DIM "A"	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0,2
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL

-

FINISH

-

DWN
D.KESSLER
CHK
C.V.TILBURG
APVD
L.V.SOEST
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
0

02APR91
23APR91
25APR91

NAME
SCREWLOCK, FEMALE HD-SERIES
-
-
SIZE
A3

CAGE CODE
00779

DRAWING NO
C-829261

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
K

CUSTOMER DRAWING

STE

TE Connectivity

1470-19 (1/15)