



PART No.,	øA NOM.	PART No.,	CABLE DIA
455616-125-*	0.125	455616-***-00	900 _μ PLAIN BUFFER FIBRE
455616-126-*	0.126	455616-***-01	2.50
455616-127-*	0.127	455616-***-02	1.80
		455616-***-03	3.00
		455616-***-04	2.10
		455616-***-05	1.20

						MATERIAL		© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH LTD.		GENERAL TOLERANCES UNLESS OTHERWISE STATED. ±0.4mm ON WHOLE NUMBERS ±0.2mm ON ONE PLACE DECIMALS ±0.1mm ON TWO PLACE DECIMALS ±1/2° ON ANGLES ±0.05mm ON DRILLED HOLES REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.		 (R) EAST GRINSTEAD, WEST SUSSEX, RH19 1RW TEL:- (01342) 410033	DEUTSCH LTD	
						HEAT TREATMENT & FINISH								
C	044000	J.T.B	es	es	12/01/04								TITLE OPTICAL CONTACT	DRAWING NUMBER
B	033637	J.V	A.V.S	K.R.M	20/05/97								ASSY- SPRUNG (SINGLE MODE) MC3 MK2	455616 (ENV)
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	DATE	APP. IED.		SCALE	5:1	DIMS. IN MILLIMETRES				