




- 1 NOMINAL WALL THICKNESS, EXPANDED.
- 2 EXPANDED INSIDE DIAMETER.
- 3 .250 MAXIMUM RECOVERED INSIDE DIAMETER.
- 4. ASSEMBLY WILL PASS ONE POUND PER SQ INCH WATER PRESSURE TEST.
- 5. TUBING SHRINK TEMPERATURE: 250°F.
- 6. OPERATING TEMPERATURE: -67°F TO 230°F.
- 7. THIS PART WILL ACCOMODATE Ø.125-Ø.375 CABLE RANGE.

1546997-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN S. WELDON 03MAR2004	Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK H. WAKEEM 03MAR2004	NAME STRAIN RELIEF ASSEMBLY, SIZE 8, MINI CPC			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ±0.02 3 PLC ±0.005 4 PLC ±0.0000 ± ANGLES FINISH		APVD H. WAKEEM 03MAR2004				
MATERIAL -		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO 1546997	RESTRICTED TO -
		APPLICATION SPEC -	SCALE 4:1		SHEET 1	OF 1
		WEIGHT -	REV A			
		CUSTOMER DRAWING				