




- 1 RECOMMENDED WIRE RANGE: 20-24 AWG COPPER STRANDED(375-1200 CMA)
- 2 RECOMMENDED INSULATION DIAMETER: 1.43-2.70mm. INSULATION < 1.76mm REQUIRES AN APPLICATOR WITH AN OVERLAP INSULATION CRIMPER.
- 3 APPLICABLE MATED PLUG HOUSING P/N:
-1971773-/*-1971776-*/*-1971876-*/
-2232265-/*-2232266-*/*-2232357-*

NOTE DELETED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
F		REVISED PER ECR-21-100678	08APR2021	VS
G		REVISED PER ECR-23-182543	27JUL2023	DS
H		REVISED PER ECR-25-236464	19MAR2025	JP
J		REVISED PER ECR-25-260470	19DEC2025	PJ

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY WU 11JUL2012	 TE Connectivity		
DIMENSIONS: mm		CHK HAPYE WU 11JUL2012			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD YUHONG MAO 11JUL2012	NAME RECEPTACLE CONTACT POWER TRIPLE LOCK		
0 PLC ± 0.5		PRODUCT SPEC 108-106118			
1 PLC ± 0.30		APPLICATION SPEC 114-106118	SIZE A2 CAGE CODE 00779 DRAWING NO 1971785		
2 PLC ± 0.30		WEIGHT -			
3 PLC ± 0.30		Customer Drawing	SCALE 6:1 SHEET 1 OF 1 REV J		
4 PLC ± 0.30					
ANGLES ± 0.5					
FINISH PRE-TIN					