





LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			P6	REVISED PER ECR-07-028917	04DEC07	HMR GP



SECTION A-A

- 1
- PRODUCT PROVIDED IN STRIP FORM ON REELS;
BREAKS MAY BE PRESENT.
- 2
- WIRE RANGE: 3300 TO 9000 CMA
- 3
- CRIMP WIDTH: .140 F TYPE
CRIMP HEIGHT (±.002)=(TOTAL CMA+14,600)/223,200
FOR APPLICATOR INFORMATION CALL:1-800-722-1111
FOR PRODUCT INFORMATION CALL:1-800-522-6752

CU-NI-SI C70260	40509-1
BRASS C26000	40509
MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 21DEC06		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK G.D.PORTA 04JAN07			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G.D.PORTA 04JAN07		NAME SPLICE	
	0 PLC ± -	PRODUCT SPEC			
	1 PLC ± -	—			
	2 PLC ± -	APPLICATION SPEC			
	3 PLC ± 0.25 [.010]	—		SIZE	
	4 PLC ± -	—		CAGE CODE	
	ANGLES ± -	WEIGHT —		DRAWING NO	
MATERIAL	FINISH	CUSTOMER DRAWING		RESTRICTED TO	
SEE TABLE	NONE			—	
				SCALE	
				10:1	
				SHEET	
				1 OF 1	
				REV	P6