


8 OBSOLETE PARTS



7 SUPERSEDED	D E L E T E D	71.12 [2.800]	28	2-644512-8-		
		68.58 [2.700]	27	2-644512-7-		
		66.04 [2.600]	26	2-644512-6-		
		63.50 [2.500]	25	2-644512-5-		
		60.96 [2.400]	24	2-644512-4-		
		58.42 [2.300]	23	2-644512-3-		
		55.88 [2.200]	22	2-644512-2-		
		53.34 [2.100]	21	2-644512-1-		
		50.80 [2.000]	20	2-644512-0-		
		48.26 [1.900]	19	1-644512-9-		
8 SUPERSEDED	S U P E R S E D E D	45.72 [1.800]	18	1-644512-8-		
		43.18 [1.700]	17	1-644512-7-		
		40.64 [1.600]	16	1-644512-6-		
		38.10 [1.500]	15	1-644512-5-		
		35.56 [1.400]	14	1-644512-4-		
		33.02 [1.300]	13	1-644512-3-		
		30.48 [1.200]	12	1-644512-2-		
		27.94 [1.100]	11	1-644512-1-		
		25.40 [1.000]	10	1-644512-0-		
		22.86 [.900]	9	-644512-9-		
7 SUPERSEDED	S U P E R S E D E D	20.32 [.800]	8	-644512-8-		
		17.78 [.700]	7	-644512-7-		
		15.24 [.600]	6	-644512-6-		
		12.70 [.500]	5	-644512-5-		
		10.16 [.400]	4	-644512-4-		
		7.62 [.300]	3	-644512-3-		
		5.08 [.200]	2	-644512-2-		
		OBSOLETE	O B S O L E T E			
		DIM A	NO.OF POSN	ASSEMBLY		

4805 (3/11)