





3D VIEW



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O.PI6830	09JAN2000	-	RDR
	B	REVISER PER PCN-24-226269	06JAN2025	AJT	MB
	C	REVISED PER PCN-25-253066	15JUL2025	UBF	MB



MATERIAL:
RECEPTACLE: PA66 GF15, GRAY
CAP: PA66 GF15, BLACK
WEDGE LOCK (INCLUDED): PBT GF30, GREEN
BUSBAR: COPPER ALLOY, NICKEL PLATED



THE 3 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 13 AMPS.
THE 5 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 26 AMPS.




ORIENTATION OF "DEUTSCH" AND "-P028" TO BE OPTIONAL.



BORDER SIGNIFIES THAT PINS 3,4,5,6,7 ARE BUSSED TOGETHER WITH
A 5 PIN BUSBAR AND PINS 1,2,8 ARE BUSSED TOGETHER WITH A 3
PIN BUSBAR.

1. MATES WITH DT06-08SA-XXXX (XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.BURKE 25AUG2000	 TE Connectivity		
DIMENSIONS: INCHES[mm]		CHK S.PALLUTH 1SEP2000			
		APVD S.BEARD 31AUG2000			
		PRODUCT SPEC 108-151009			
		APPLICATION SPEC 114-151009	NAME DT 8 WAY RECEPTACLE KEY ARRANGEMENT A 5 AND 3 PIN BUSBAR - NICKEL PLATED COLOR: GREY		
		WEIGHT 22 g	SIZE A3	CAGE CODE 00779	RESTRICTED TO -
MATERIAL		FINISH -	DRAWING NO C-DT04-08PA-P028	SCALE 2.000	REV C
CUSTOMER DRAWING		SHEET 1 OF 1			