






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N2	ECR-26-269705	06FEB2026	ABS	PS



RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

		35.56 [1.400]	14	37.69 [1.484]	15	6-146132-3
OBSOLETE		33.02 [1.300]	13	35.15 [1.384]	14	6-146132-2
OBSOLETE		30.48 [1.200]	12	32.61 [1.284]	13	6-146132-1
OBSOLETE		27.94 [1.100]	11	30.07 [1.184]	12	6-146132-0
OBSOLETE		25.40 [1.000]	10	27.53 [1.084]	11	5-146132-9
OBSOLETE		22.86 [.900]	9	24.99 [.984]	10	5-146132-8
OBSOLETE		20.32 [.800]	8	22.45 [.884]	9	5-146132-7
		17.78 [.700]	7	19.91 [.784]	8	5-146132-6
OBSOLETE		15.24 [.600]	6	17.37 [.684]	7	5-146132-5
		12.70 [.500]	5	14.83 [.584]	6	5-146132-4
OBSOLETE		10.16 [.400]	4	12.29 [.484]	5	5-146132-3
		7.62 [.300]	3	9.75 [.384]	4	5-146132-2
		5.08 [.200]	2	7.21 [.284]	3	5-146132-1
OBSOLETE		15.24 [.600]	6	17.37 [.684]	7	4-146132-5
6-146132-3		35.56 [1.400]	14	37.69 [1.484]	15	1-146132-3
OBSOLETE		33.02 [1.300]	13	35.15 [1.384]	14	1-146132-2
		30.48 [1.200]	12	32.61 [1.284]	13	1-146132-1
OBSOLETE		27.94 [1.100]	11	30.07 [1.184]	12	1-146132-0
OBSOLETE		25.40 [1.000]	10	27.53 [1.084]	11	146132-9
OBSOLETE		22.86 [.900]	9	24.99 [.984]	10	146132-8
OBSOLETE		20.32 [.800]	8	22.45 [.884]	9	146132-7
5-146132-6		17.78 [.700]	7	19.91 [.784]	8	146132-6
OBSOLETE		15.24 [.600]	6	17.37 [.684]	7	146132-5
5-146132-4		12.70 [.500]	5	14.83 [.584]	6	146132-4
OBSOLETE		10.16 [.400]	4	12.29 [.484]	5	146132-3
5-146132-2		7.62 [.300]	3	9.75 [.384]	4	146132-2
5-146132-1		5.08 [.200]	2	7.21 [.284]	3	146132-1
	PLATING	C	B	A	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09SEP94 J. KNOUB CHK 09SEP94 G. DUBNICZKI APVD 09SEP94 G. DUBNICZKI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± .- 1 PLC ± .- 2 PLC ± .- 3 PLC ± .- 4 PLC ± .- ANGLES ± ° ' 30"		NAME SURFACE MOUNT HEADER ASSY, MOD II, B/A, VERT, SINGLE ROW, .100 C/L .025 SQ. POST -	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO A1 00779	
MATERIAL 		FINISH SEE TABLE		RESTRICTED TO - SCALE 10:1 SHEET 1 OF 1 REV N	
		WEIGHT -		CUSTOMER DRAWING	