



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		L2	REVISED PER ECO-11-004587	11MAR11	RK	HMR

- 6

REDUCED PACKAGE QUANTITY.
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

- 1CONTINUOUS STRIP ON REEL.
- 2WIRE SIZE IS [#22-#18] AWG.
- 3INSULATION RANGE IS 2.03-2.79 [.080-.110] DIA.
- 4FOR FOREIGN PRODUCTION ONLY REELED WITH
PAPER INTERLEAVE
- 5PRELIMINARY - NOT FOR PRODUCTION



6	TIN PLATING	M 3.5 - [#6]	3.68 [.145]	5	42037-9
	TIN PLATING	[#10]	5.00 [.197]	5	42037-8
4	OBSOLETE	TIN PLATING	M 4 - [#8]		42037-7
OBSOLETE	4	TIN PLATING	[#10]		42037-6
		TIN PLATING	[#10]		42037-2
		TIN PLATING	M 4 - [#8]		42037-1
		TIN PLATING	M 3.5 - [#6]		42037
FINISH		STUD SIZE	D DIM	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

082 BRASS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.25 [.010]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

SEE TABLE

DWN
JR RUTH
01AUG00

CHK
MS FEHER
01AUG00

APVD
D DECKER
01AUG00

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

TE Connectivity

NAME
RING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-42037

-

CUSTOMER DRAWING

SCALE 8:1

SHEET 1 OF 1

REV L2