





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	30DEC2015	DL	CW
	B	ECR-21-122216	09DEC2021	WQR	CW



OTHER SPEC REFER TO
PN T2071164101-000

HI6BP-T4-F
T2071164201-000
DOCKING FRAME FOR HMN INSERTS_FIXED
4 MODULES

SPACING OF TWO PANELS AT CLOSE STATUS

T2071164201-000	H16BP-T4-F DOCKING FRAME FOR HMN INSERTS_FIXED HMN 塑胶框架_固定端
T2071164101-000	H16BP-T4-M DOCKING FRAME FOR HMN INSERTS_FLOATING HMN 塑胶框架_浮动端
PART NUMBER 料 号	PART DESCRIPTION 描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 30DEC2015		 TE Connectivity	
		CHK CHRIS WANG 30DEC2015			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME H16BP-T4-M/F DOCKING FRAME FOR HMN INSERTS 4 MODULES	
		APVD XU XINAG 30DEC2015 PRODUCT SPEC 108-137168 APPLICATION SPEC 114-137168			
MATERIAL - -		FINISH - -		SIZE A2	
		WEIGHT -		CAGE CODE -	
		CUSTOMER DRAWING		DRAWING NO C-T2071164X01000	
				RESTRICTED TO -	
				SCALE 4.5	
				SHEET 1 OF 1	
				REV B	