





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	02MAR2016	N.P	X.X
	A1	PER ECR-16-010253	21JUL2016	N.P	X.X



- NOTES:
- 1. TECHNICAL DATA: SEE TABLE 1
 - 2. STRIP AND RETAIN THE INSULATION
 - 3. RECOMMEND TORQUE 0.4Nm
 - 4. TE LABLE AREA.
 - 5. - **: CABLE LENGHT. -0.5:0.5m, -1.0:1.0m, -1.5:1.5m...
 - 6. ALL PRODUCT MUST COMPLIANCE WITH ROHS AND REACH.

- 注意事项
- 1. 技术参数：见表1
 - 2. 剥线并保留绝缘层；
 - 3. 推荐扭矩0.4Nm；
 - 4. TE 标签位置；
 - 5. - **线长：-0.5:0.5m, -1.0:1.0m, -1.5:1.5m
 - 6. 产品必须符合ROHS与REACH.

-	-	TE LABLE	9
	BRASS	SHIELDING	8
	STEEL	WAVE WASHER	7
-	-	CABLE	6
BLUE COLOR	POLYURETHANE	OVER-MOLDING	5
-	COPPER ALLOY	COUPLING NUT	4
	RUBBER	O-RING	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	STANDARD: -001: 0.5m -002: 1.0m -003: 1.5m -004: 3.0m -005: 5.0m -006: 7.0m -007: 10.0m CUSTOMIZATION: - **: 00.0m -001: **.5m	FIXED: -40°C~80°C FLXIBLE: -25°C~80°C	GRAY	PUR (UL)	RPC-M8-FR-4CON-PUR-**SH	5	4	T4061420004-00X
					RPC-M8-FR-3CON-PUR-**SH	5	3	T4061420003-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-FR-4CON-PVC-**SH	5	4	T4061410004-00X
					RPC-M8-FR-3CON-PVC-**SH	5	3	T4061410003-00X
CABLE CHARACTERISTIC	LENGTH "L"	CABLE TEMP. RANGE	JACKET COLOR	JACKET MATERIAL	TYPE		POS.	PART NUMBER

TABLE 1		
TECHNICAL DATA	T40614X0003-00X	T40614X0004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
TBD
material_2

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.50
2 PLC ±0.35
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

finish_spec_2

DWN Nick Pan 29JAN2016
CHK Kobby Zhao 29JAN2016
APVD Xiang Xu 29JAN2016

PRODUCT SPEC
108-106140

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

M8 CABLE ASSEMBLY RIGHT ANGLE SHIELDED, FEMALE, SINGLE ENDED

SIZE A2

CAGE CODE -

DRAWING NO. ©T40614000X00X

RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 1 REV A1

1471-9 (3/13)