


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REVISED PER ECN-25-344960	01SEP2025	AD	JM



- D

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PACKAGE 2	108-60121	30 u "	45.0	8.0	44.5	91	70	73.15	89	71.65	164	7-2337939-4	
PACKAGE 1		30 u "	86.5		44.5	91	70	73.15	89	71.65	164	5-2337939-8	
PACKAGE 4		30 u "	53.5		28	58	37	40.15	56	38.65	98	5-2337939-7	
PACKAGE 3		30 u "	36.5		19.5	41	20	23.15	39	21.65	64	5-2337939-6	
NA		30 u "	22.5		12.5	27	6	9.15	25	7.65	36	5-2337939-5	
PACKAGE 1	108-60121-1	30 u "	10.0		44.5	91	70	73.15	89	71.65	164	5-2337939-4	
PACKAGE 4		30 u "	10.0		28	58	37	40.15	56	38.65	98	5-2337939-3	
PACKAGE 3		30 u "	10.0		19.5	41	20	23.15	39	21.65	64	5-2337939-2	
NA		30 u "	10.0		12.5	27	6	9.15	25	7.65	36	5-2337939-1	
PACKAGE 1		15 u "	86.5		44.5	91	70	73.15	89	71.65	164	4-2337939-8	
PACKAGE 4		15 u "	53.5		28	58	37	40.15	56	38.65	98	4-2337939-7	
PACKAGE 3		15 u "	36.5		19.5	41	20	23.15	39	21.65	64	4-2337939-6	
NA		15 u "	22.5		12.5	27	6	9.15	25	7.65	36	4-2337939-5	
PACKAGE 1		15 u "	10.0		44.5	91	70	73.15	89	71.65	164	4-2337939-4	
PACKAGE 4		15 u "	10.0		28	58	37	40.15	56	38.65	98	4-2337939-3	
PACKAGE 3		15 u "	10.0		19.5	41	20	23.15	39	21.65	64	4-2337939-2	
NA		15 u "	10.0		12.5	27	6	9.15	25	7.65	36	4-2337939-1	
PACKAGE 1		108-60121-1	G/F		86.5	44.5	91	70	73.15	89	71.65	164	3-2337939-8
PACKAGE 4			G/F		53.5	28	58	37	40.15	56	38.65	98	3-2337939-7
PACKAGE 3			G/F		36.5	19.5	41	20	23.15	39	21.65	64	3-2337939-6
NA	G/F		22.5	12.5	27	6	9.15	25	7.65	36	3-2337939-5		
PACKAGE 1	G/F		10.0	44.5	91	70	73.15	89	71.65	164	3-2337939-4		
PACKAGE 4	G/F		10.0	28	58	37	40.15	56	38.65	98	3-2337939-3		
PACKAGE 3	G/F		10.0	19.5	41	20	23.15	39	21.65	64	3-2337939-2		
NA	G/F	10.0	12.5	27	6	9.15	25	7.65	36	3-2337939-1			
PACKAGE 2	108-60121	30 u "	NA	44.5	91	70	73.15	89	71.65	164	2-2337939-5		
PACKAGE 1		30 u "	NA	44.5	91	70	73.15	89	71.65	164	2-2337939-4		
PACKAGE 4		30 u "	NA	28	58	37	40.15	56	38.65	98	2-2337939-3		
PACKAGE 3		30 u "	NA	19.5	41	20	23.15	39	21.65	64	2-2337939-2		
NA		30 u "	NA	12.5	27	6	9.15	25	7.65	36	2-2337939-1		
PACKAGE 1	108-60121-1	15 u "	NA	44.5	91	70	73.15	89	71.65	164	6-2337939-4		
PACKAGE 4		15 u "	NA	28	58	37	40.15	56	38.65	98	6-2337939-3		
PACKAGE 3		15 u "	NA	19.5	41	20	23.15	39	21.65	64	6-2337939-2		
NA		15 u "	NA	12.5	27	6	9.15	25	7.65	36	6-2337939-1		
PACKAGE 1		G/F	NA	44.5	91	70	73.15	89	71.65	164	2337939-4		
PACKAGE 4		G/F	NA	28	58	37	40.15	56	38.65	98	2337939-3		
PACKAGE 3		G/F	NA	19.5	41	20	23.15	39	21.65	64	2337939-2		
NA	G/F	NA	12.5	27	6	9.15	25	7.65	36	2337939-1			
PACKING SPEC	PRODUCT SPEC	GOLD PLATING	W	V	J	D	N	C	B	A	POS.	PART NUMBER	
			MYLAR SIZE (PAGE 4)										

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±0.050
4 PLC ±-
ANGLES ±-
FINISH

-
-

DWN
FRED LIU
CHK
HOPE LU
APVD
HOPE LU
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

12JUN2018
12JUN2018
12JUN2018
-
-
-
-

TE Connectivity

NAME
PCI EXPRESS CARD EDGE CONNECTOR
GEN4 , STANDARD VERSION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2337939

RESTRICTED TO
-

SCALE
3:1


SHEET
2

OF
7


REV
F1

1471-9 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT



ADD-IN CARD EDGE-FINGER DIMENSION

164	92.00	70	73.15	72.15	A1,B17,B31,B48,B81
98	59.00	37	40.15	39.15	A1,B17,B31,B48
64	42.00	20	23.15	22.15	A1,B17,B31
36	28.00	6	9.15	8.15	A1,B17
POS.	DIM. E	DIM. F	DIM. G	DIM. H	"K"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU 12JUN2018		 TE Connectivity			
		CHK HOPE LU 12JUN2018					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PCI EXPRESS CARD EDGE CONNECTOR GEN4 , STANDARD VERSION			
		APVD HOPE LU 12JUN2018					
		PRODUCT SPEC -					
		APPLICATION SPEC -					
MATERIAL - -		FINISH - -		SIZE A2	CAGE CODE 00779	DRAWING NO C-2337939	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 3:1	SHEET 3 of 7	REV F1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FRONT VIEW

REAR VIEW

36POS AS SHOWN

FRONT VIEW

REAR VIEW

64POS AS SHOWN

FRONT VIEW

REAR VIEW

98POS AS SHOWN

FRONT VIEW

REAR VIEW

164POS AS SHOWN

W

REF

V

REF

J

MYLAR SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±

0.3

1 PLC

±

0.20

2 PLC

±

0.050

3 PLC

±

0.050

4 PLC

±

0.050

ANGLES

±

0.050

FINISH

±

0.050

MATERIAL

-

-

DWN

FRED LIU

12JUN2018

CHK

HOPE LU

12JUN2018

APVD

HOPE LU

12JUN2018

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR

GEN4 , STANDARD VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2337939

-

-

SCALE

3:1

SHEET

4 OF 7

REV

F1

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A


A



PACKAGE 1



PACKAGE 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU 12JUN2018	 TE Connectivity			
		CHK HOPE LU 12JUN2018				
DIMENSIONS:		APVD HOPE LU 12JUN2018	NAME PCI EXPRESS CARD EDGE CONNECTOR GEN4 , STANDARD VERSION			
mm		PRODUCT SPEC				
		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			A2	00779	C-2337939	-
MATERIAL		WEIGHT	CUSTOMER DRAWING			
			SCALE	3:1	SHEET	5 OF 7
					REV	F1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A

A



PACKAGE 3



PACKAGE 4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRED LIU CHK HOPE LU APVD HOPE LU		12JUN2018 12JUN2018 12JUN2018		 TE Connectivity					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PCI EXPRESS CARD EDGE CONNECTOR GEN4 , STANDARD VERSION							
		0 PLC ±- 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.050 4 PLC ±- ANGLES ±- FINISH									
MATERIAL - -		- -		SIZE A2		CAGE CODE 00779		DRAWING NO C-2337939		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 3:1		SHEET 6 OF 7		REV F1			

