




SUPERSEDED BY 1.5.1610



PIPE SIZE	"A" DIM BARREL CRIMP	"G" DIM INSUL CRIMP
GAGE	GO NO GO	GO NO GO FIN AT "1" FIN AT "4"
18-16	.131 .134	.030 .110
14	.151 .154	.040 .120



18-16
BARREL INSERTS

14
BARREL INSERTS

ERNEST CHAND

MEDIATION CRIMINAL

NOTES

1. WHEN PLUG OR SLUG GAGING OF BARREL CRIMP IT IS IMPORTANT TO NOTE THAT DIM. "A" IS THE FIGURE REQD.

2. GAGE DIMENSIONS APPLY WHEN TOOL IS HOTTERED BUT NOT UNDER PRESSURE.

[illegible][illegible]

DR
AMP PRODUCTS COVERED BY
©1967 BY AMP INCORP
Dr. Winkler 3-2-67

CR
3-2-67

DR
3-2-67

3-10-67

PATENTED. ALL RIGHTS RESERVED. PATENTS AND/OR PATENTS PENDING.		CUSTOMER COPY REFERENCE ONLY	
MATERIAL AND FINISH		 AMP INCORPORATED HARRISBURG, PENNA.	
WIRE - RANGE - INSULATION 18-16 & 14-1	TOLEANCE EXCEPT ± .015 = 1° 0'	SCALE 1-1	
TYPE P.I.D.S. STRATOTHERM	CLASS	LOG M B	INO 69693-1
NAME: "T" HEAD ASSEMBLY		REV. 011	

RECEIVED MAY 20 1968

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

PRINT DIST