




REV. B


DCO 300781

TOLERANCES $\pm .010"$ - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C
 RESISTANCE 320 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 28 VDC
 MUST OPERATE 13.5 VDC MAX.
 MUST RELEASE 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 Hz TO 3000 Hz @ 30 g's
 SHOCK 200 g's 6 MS. DURATION
 TEMPERATURE -70 °C TO +125 °C
 NOTES: OPERATE, RELEASE 10 MS MAX.
 CONTACT STABILIZATION 2.5 MS MAX.
 CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL
 TO 10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE,
 100,000 OPERATIONS

DR. B.D. 05MAR2008

CK. 3/7/08 J.M.B.

Tyco Electronics

©COPYRIGHT 2005
 TYCO ELECTRONICS CORPORATION
 ALL INTERNATIONAL RIGHTS RESERVED

CUST. NO. M83536/9-019M REV. ---

TE NUMBER
 9-1617748-2

CII PART NUMBER
 FCA-210-0919M